

Elevate High Density Fibre Optic Cassettes

Multimode, Base16



Product Overview

The Elevate Multimode Base16 cassette forms part of a modular high-density fibre solution, designed to support higher speed multimode connectivity in rack mount environments. Incorporating Senko low loss Base16 MPO connectivity, the cassette enables a structured transition to LC shuttered adaptors at the front patching field, supporting emerging parallel optics applications. When installed within a compatible high density chassis, the solution provides scalable fibre management and optimised rack utilisation.

- ✓ High density 16 fibre LC to MPO cassette
- ✓ Senko low loss MPO plus male
- ✓ 16 fibre MPO at rear
- ✓ Access test data via online Test Trace
- ✓ Compatible with Elevate High Density Chassis
- ✓ OM4 & OM5 options



Please note that this datasheet focuses on the range of Elevate Multimode Base16 Fibre Optic Cassettes. Datasheets for other options can be found on the Elevate website:

Product Specifications

Feature	Values
Number of fibres	16
Fibre type	OM4 / OM5
Rear connectivity	
Base16	1 x MPO 16F male / female (keyup)
Rear connectivity colour	Grey
Cassette colour	White (RAL9003) Black (RAL 9004)
MPO Typical Insertion loss	0.15dB
MPO Maximum Insertion loss	0.25dB
MPO Return loss	>25dB
LC Insertion loss	<0.25dB
LC Return loss	>55dB
Front connectivity	LC (Key up)
Front connectivity colour	Violet (OM4) Lime Green (OM5)
Laser dispersal shutter	Yes
Operating temperature	-20 to +70
Storage temperature	-20 to +85

Product Features Explained



All Elevate MPO solutions are built on Senko low loss, best in class connectivity.



Each cassette is factory tested and test data is accessed via the QR code attached to the cassette and our test trace portal.

**The Elevate Cassettes are compatible with the Elevate High Density Chassis.
Chassis Part Number Range - 208-4XX**




Also available in white.

A full range of chassis are available:



Product Drawing



Applicable standards

Compliance with International Standards ISO 11801, EN 50173 and ANSI/TIA 568-E, necessitates that this product/component adheres to all relevant normative references specified within these standards.

Standard	Detail
Directive 2008/98/EC (WFD)	Waste Framework Directive — compliant. Implemented in the UK through the Waste (England and Wales) Regulations 2011 (SI 2011 No. 988).
ECHA SCIP Database	Compliant; product does not contain SVHCs (Substances of Very High Concern) as defined under REACH Article 33(1). Submission obligations met under EU REACH and UK REACH.
Regulation (EU) 2019/1021 (POPs)	EU Regulation on Persistent Organic Pollutants — compliant. For Great Britain, compliance is aligned with the Persistent Organic Pollutants (Amendment) (EU Exit) Regulations 2020 (SI 2020 No. 1355).
Directive 2011/65/EU (RoHS II)	Restriction of the Use of Certain Hazardous Substances in Electrical and Electronic Equipment — compliant. Applies within EU member states.
Directive (EU) 2015/863 (RoHS III)	Amending Directive 2011/65/EU to add four phthalates (DEHP, BBP, DBP, DIBP) to Annex II — compliant.
UK SI 2012 No. 3032	The Restriction of the Use of Certain Hazardous Substances in Electrical and Electronic Equipment Regulations 2012 (UK RoHS) — compliant for Great Britain. Retained EU law, as amended by the Product Safety and Metrology (Amendment etc.) (EU Exit) Regulations 2019.

Elevate High Density Fibre Optic Multimode Base16 Cassettes are available in the following options:




To Achieve Correct Polarity


Trunk cable

To achieve the correct polarity use standard Method B female trunks

Polarity A	Polarity B	Polarity C
Cassette 1 use cassette Type B	Cassette 1 use cassette Type B	Cassette 1 use cassette Type B
Cassette 2 use cassette Type A	Cassette 2 use cassette Type B	Cassette 2 use cassette Type C



Polarity illustration shown is representative. The same Method B trunk polarity applies across all Elevate HD Fibre Cassette variants, including Base 8, 12, 16 and 24 in both singlemode and multimode configurations.




Also available in black.

Part Number Table: Multimode - Base16 - Male

Part Number	Description
16F - OM4	
208-392-TYPE-A	Elevate HD Base16 - 16 Fibre OM4 LC-MPO male Cassette Type A White
208-392-TYPE-B	Elevate HD Base16 - 16 Fibre OM4 LC-MPO male Cassette Type B White
208-392-TYPE-C	Elevate HD Base16 - 16 Fibre OM4 LC-MPO male Cassette Type C White
208-392-TYPE-A-BK	Elevate HD Base16 - 16 Fibre OM4 LC-MPO male Cassette Type A Black
208-392-TYPE-B-BK	Elevate HD Base16 - 16 Fibre OM4 LC-MPO male Cassette Type B Black
208-392-TYPE-C-BK	Elevate HD Base16 - 16 Fibre OM4 LC-MPO male Cassette Type C Black
16F - OM5	
208-592-TYPE-A	Elevate HD Base16 - 16 Fibre OM5 LC-MPO male Cassette Type A White
208-592-TYPE-B	Elevate HD Base16 - 16 Fibre OM5 LC-MPO male Cassette Type B White
208-592-TYPE-C	Elevate HD Base16 - 16 Fibre OM5 LC-MPO male Cassette Type C White
208-592-TYPE-A-BK	Elevate HD Base16 - 16 Fibre OM5 LC-MPO male Cassette Type A Black
208-592-TYPE-B-BK	Elevate HD Base16 - 16 Fibre OM5 LC-MPO male Cassette Type B Black
208-592-TYPE-C-BK	Elevate HD Base16 - 16 Fibre OM5 LC-MPO male Cassette Type C Black

Part Number Table: Multimode - Base16 - Female



Also available in black.

Part Number	Description
16F - OM4	
208-292-TYPE-A	Elevate High Density Base16 - 16 Fibre OM4 LC-MPO Female Cassette Type A White
208-292-TYPE-B	Elevate High Density Base16 - 16 Fibre OM4 LC-MPO Female Cassette Type B White
208-292-TYPE-C	Elevate High Density Base16 - 16 Fibre OM4 LC-MPO Female Cassette Type C White
208-292-TYPE-A-BK	Elevate High Density Base16 - 16 Fibre OM4 LC-MPO Female Cassette Type A Black
208-292-TYPE-B-BK	Elevate High Density Base16 - 16 Fibre OM4 LC-MPO Female Cassette Type B Black
208-292-TYPE-C-BK	Elevate High Density Base16 - 16 Fibre OM4 LC-MPO Female Cassette Type C Black
16F - OM5	
208-792-TYPE-A	Elevate High Density Base16 - 16 Fibre OM5 LC-MPO Female Cassette Type A White
208-792-TYPE-B	Elevate High Density Base16 - 16 Fibre OM5 LC-MPO Female Cassette Type B White
208-792-TYPE-C	Elevate High Density Base16 - 16 Fibre OM5 LC-MPO Female Cassette Type C White
208-792-TYPE-A-BK	Elevate High Density Base16 - 16 Fibre OM5 LC-MPO Female Cassette Type A Black
208-792-TYPE-B-BK	Elevate High Density Base16 - 16 Fibre OM5 LC-MPO Female Cassette Type B Black
208-792-TYPE-C-BK	Elevate High Density Base16 - 16 Fibre OM5 LC-MPO Female Cassette Type C Black